

# Arc View 465 XL

Specification Sheet (Part/REF # 243802)



The 465 XL controller has an extra large display with 4 sensor channels for controlling one to four Incyte or Dencytee sensors.

## Product Specifications

<b>Dimensions (W x D x H)</b>	439 x 115 x 365 mm
<b>Analog Output</b>	Optional AUX to Analog Output Box 4-20 mA
<b>Digital Interface</b>	Ethernet connection with RJ45 (OPC XML-DA) RS485 Modbus (max. 31 addresses) USB 2.0
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Stainless Steel
<b>Measuring Channels</b>	4
<b>Power Supply</b>	24 VDC; 2.5 A
<b>Operating Humidity</b>	0 to 80 %
<b>Operating Temperature Range</b>	-10 to 45 °C

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/sensors/243802>

**Spec. Version B**