


Septa, High Temp, 11.0 mm DIA (12/PK)

Specification Sheet (Part/REF # 75807)



High Temperature Septa is made of preconditioned PTFE/silicone rubber and is 3.175 mm (0.125 in) thick. The average life of these septa is up to 100 injections with a 26s gauge needle. The maximum operating temperature is 212° C.

Product Specifications

Diameter	11 mm (0.433 inch)
Maximum Temperature	212°C / 414°F
Material	PTFE Backed Silicone Rubber
Thickness	3.18 mm (0.125 inch)
Sales Quantity	12 septa per pack

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/laboratory-products/gc-septa/75807>

Spec. Version B