

Septa, High Temp, 9.5 mm DIA (12/PK)

Specification Sheet (Part/REF # 75804)

High Temperature Septa is made of preconditioned PTFE/silicone rubber and is 3.175 mm (0.125 in) thick. The average life of these septa is up to 100 injections with a 26s gauge needle. The maximum operating temperature is 212° C.

Product Specifications

Diameter	9.5 mm (0.374 inch)
Maximum Temperature	212°C / 414°F
Material	PTFE Backed Silicone Rubber
Thickness	3.18 mm (0.125 inch)
Sales Quantity	12 septa per pack

Specifications are subject to change without notice

Spec. Version B

<https://www.hamiltoncompany.com/laboratory-products/gc-septa/75804>