

# Septa, 3-Layer, 11.0 mm DIA (12/PK)

Specification Sheet (Part/REF # 76007)



Three Layer Septa is made of preconditioned silicone rubber and is 3.81 mm (0.150 in) thick. The average life of these septa is up to 100 injections with a 26s gauge needle. The maximum operating temperature is 200° C.

## Product Specifications

Diameter	11 mm (0.433 inch)
Maximum Temperature	200°C / 392°F
Material	Laminated Silicone Rubber
Thickness	3.81 mm (0.150 inch)
Sales Quantity	12 septa per pack

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/laboratory-products/gc-septa/76007>

Spec. Version B