

HxSil C8 Analytical Guard Column Starter Kit (1 holder, 2 cartridges), Stainless Steel

Specification Sheet (Part/REF # 79458)



Protect your HxSil C8 column.

Product Specifications

Separation Mode	Reversed-Phase
Stationary Phase	HxSil C8
Format	Guard Cartridge Kit
Hardware Inner Diameter	2.1 mm
Hardware Length	20 mm
Particle Size	10 µm
Packing Material Type	Silica
Guard Column Size	Analytical
Hardware Material	Stainless Steel
Max Pressure	5,000 psi
Mobile Phase Limits	pH 2.0 - 7.5
Compound Classification	General Purpose
UOM	1 holder, 2 cartridges

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/laboratory-products/hplc-columns/79458>

Spec. Version B