

HxSil C8 Semiprep/Preparative Guard Column Replacement Cartridges (2/pk), Stainless Steel

Specification Sheet (Part/REF # 79136)



Protect your HxSil C8 column.

Product Specifications

Separation Mode	Reversed-Phase
Stationary Phase	HxSil C8
Format	Replacement Guard Cartridge
Hardware Inner Diameter	4.6 mm
Hardware Length	20 mm
Particle Size	10 µm
Packing Material Type	Silica
Guard Column Size	Semiprep/Preparative
Hardware Material	Stainless Steel
Max Pressure	5,000 psi
Mobile Phase Limits	pH 2.0 - 7.5
Compound Classification	General Purpose
UOM	2/pk

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/laboratory-products/hplc-columns/79136>

Spec. Version B