

PRP-X500, 30-50 µm Bulk Resin

Specification Sheet (Part/REF # 79596)



Pack your own column.

Product Specifications

Separation Mode	Anion Exchange
Stationary Phase	PRP-X500
Format	Bulk Resin
Particle Size	30-50 µm
Packing Material Type	Poly(methacryl amido-propyl trimethyl ammonium chloride)
Pore Size	Superficially Porous
Particle Surface Area (m²/cm³)	1.4
Pore Volume (cm³/g)	0.0063
Max Pressure	5,000 psi
Exchange Capacity	1.6 meq/gm
UOM	per gram

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/laboratory-products/hplc-columns/79596>

Spec. Version B