

1/4"-28 Fittings and Washers (12 gauge) 10/pk

Specification Sheet (Part/REF # 88807)

Product Specifications

Washer Material	Stainless Steel
Gauge	12 gauge
Washer Inner Diameter (I.D.)	0.128 in / 3.251 mm
Washer Outer Diameter (O.D.)	0.200 in / 5.080 mm
Sales Quantity	10 per pack

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/laboratory-products/fittings/88807>

Spec. Version B