

ODO Cap H3

Specification Sheet (Part/REF # 10068400)



Strengthened luminophore matrix for better temperature stability with fast response time. The perfect cap for most biopharmaceutical applications. Compatible with VisiFerm mA and VisiFerm RS485.

Product Specifications

Wetted Parts	Stainless Steel 1.4435 EPDM (Ethylene propylene elastomer) Silicone - FDA 21 CFR 177.2600 VMQ (Silicone elastomer) See compliance details in Material Specification document
Surface Quality of Steel	Ra < 0.4 µm (N5)
Serial Number	Yes
Response Time	t98% < 30 s at 25 °C
Autoclavable	Yes, max. Temperature 140 °C
Steam Sterilizable	Yes, max. Temperature 140 °C
Operating Temperature Range	-20 to 140 °C

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/process-analytics/sensors/10068400>

Spec. Version D