

# ODO Cap H3

Specification Sheet (Part/REF # 10068400)



Strengthened luminophore matrix for better temperature stability with fast response time. The perfect cap for most biopharmaceutical applications. Only compatible with the VisiFerm mA.

## Product Specifications

|                                    |  |
|------------------------------------|--|
| <b>Wetted Parts</b>                | Stainless Steel 1.4435<br>EPDM (Ethylene propylene elastomer)<br>Silicone - FDA 21 CFR 177.2600<br>VMQ (Silicone elastomer)<br>See compliance details in Material Specification document |
| <b>Surface Quality of Steel</b>    | Ra < 0.4 µm (N5)   |
| <b>Serial Number</b>               | Yes  |
| <b>Response Time t98%</b>          | < 30 s at 25 °C  |
| <b>Autoclavable</b>                | Yes, max. Temperature 140 °C   |
| <b>Steam Sterilizable</b>          | Yes, max. Temperature 140 °C   |
| <b>Operating Temperature Range</b> | -20 to 140 °C  |

Specifications are subject to change without notice

**Spec. Version B**

<https://www.hamiltoncompany.com/process-analytics/sensors/10068400>