

# ODO Cap H4

Specification Sheet (Part/REF # 10078261)



Strengthened luminophore matrix for better temperature stability with chemically resistant and hygienic design. Only compatible with the VisiFerm mA.

## Product Specifications

<b>Wetted Parts</b>	Stainless Steel 1.4435 PTFE (Polytetrafluoroethylene) EPDM (Ethylene propylene elastomer) Silicone - FDA 21 CFR 177.2600 VMQ (Silicone elastomer) See compliance details in Material Specification document
<b>Surface Quality of Steel</b>	Ra < 0.4 µm (N5)
<b>Serial Number</b>	Yes
<b>Response Time t98%</b>	< 60 s at 25 °C
<b>Autoclavable</b>	Yes, max. Temperature 140 °C
<b>Steam Sterilizable</b>	Yes, max. Temperature 140 °C
<b>Operating Temperature Range</b>	-20 to 140 °C

Specifications are subject to change without notice

**Spec. Version B**

<https://www.hamiltoncompany.com/process-analytics/sensors/10078261>