

Arc View 465 XL

Specification Sheet (Part/REF # 243802)



The 465 XL Controller has an extra large display with 4 sensor channels for controlling one to four Incyte or Dencytee sensors.

Product Specifications

Dimensions (W x D x H)	439 x 115 x 365 mm
Analog Output	Optional AUX to Analog Output Box 4-20 mA
Digital Interface	Ethernet connection with RJ45 (OPC XML-DA) RS485 Modbus (max. 31 addresses) USB 2.0
Operating Voltage	24 VDC
Housing Material	Stainless Steel
Measuring Channels	4
Power Supply	24 VDC; 2.5 A
Operating Humidity	0 to 80 %
Operating Temperature Range	-10 to 45 °C

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/process-analytics/sensors/243802>

Spec. Version B