

3 m Cable M12-8 Pole / Open End

Specification Sheet (Part/REF # 355320)



8-pole M12-8 Arc Sensor Cable, designed to connect the Arc WI 2G adapter BT to a data recorder, indicator, control unit or PCS with analog I/O - 3 Meter length.

Product Specifications

Electrical Connector	M12-8 Pole A-Coded / Open End
Length	3 m
Max. Diameter	6 mm
Material Outer Cover	PU
Shield	Yes
Operating Temperature Range	-20 to 85 °C
Protection Rating	IP 68 (M12 connector)

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/process-analytics/sensors/355320>

Spec. Version B