

# 1 m Cable VP8 / Open End / Power Plug

Specification Sheet (Part/REF # 355194-xx)



This cable provides 24VDC power for Arc and VisiFerm ECS sensors. Open leads allow direct wiring to transmitters, PLC and PCS systems.

## Product Specifications

Electrical Connector	VP8 / Open End / Power Plug
Length	1 m
Max. Diameter	7,5 mm
Power Supply	110 to 240 VAC to 24 VDC
Material Outer Cover	PVC
Shield	Yes
Temperature Range	-30 to 80 °C
Protection Rating	IP 68 (VP8 connector)

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/process-analytics/sensors/355194-xx>

Spec. Version D