


# 3 m Cable VP8 / Open End

Specification Sheet (Part/REF # 355218)



Variopin VP8 cables for direct wiring with power to transmitters and other devices - 3 Meter length.

## Product Specifications

Electrical Connector	VP8 / Open End
Length	3 m
Max. Diameter	7,5 mm
Material Outer Cover	PVC
Shield	Yes
Operating Temperature Range	-30 to 80 °C
Protection Rating	IP 68 (VP8 connector)

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/process-analytics/sensors/355218>

Spec. Version B