

# Calibration Station

Specification Sheet (Part/REF # 243575)



Calibration station used for validation / calibration of sensors in gaseous media. Equipped with two inlets for a wide array of test scenarios.

## Product Specifications

|                               |                                  |
|-------------------------------|----------------------------------|
| <b>For Sensors with</b>       | 120 mm, 12 mm, PG13,5            |
| <b>Dimensions (W x D x H)</b> | 137 x 115 x 186 mm               |
| <b>Housing Material</b>       | Black PEEK with aluminium holder |
| <b>Ø O.D. Fitting</b>         | 8,7 mm                           |
| <b>Ø I.D. Fitting</b>         | 3,5 mm                           |
| <b>Pressure Range bar g</b>   | 0 to 12 bar                      |

Specifications are subject to change without notice

**Spec. Version B**

<https://www.hamiltoncompany.com/process-analytics/sensors/243575>