

Membrane Kit CIP

Specification Sheet (Part/REF # 237126)



Product Specifications

Membrane Cap	Optiflow CIP
Wetted Parts	Stainless Steel 1.4435 VMQ (Silicone elastomer)
O-ring Material	25 mm: FKM; 12 mm: -
Surface Quality of Steel	Ra < 0.4 µm (N5, electropolished)
Serial Number	Yes

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/process-analytics/sensors/237126>

Spec. Version B