

# Membrane Kit FDA

Specification Sheet (Part/REF # 237140)

## Product Specifications

<b>Membrane Cap</b>	Optiflow FDA
<b>Wetted Parts</b>	Stainless Steel 1.4435 EPDM (Ethylene propylene elastomer) Silicone - FDA 21 CFR 177.2600 VMQ (Silicone elastomer) See compliance details in Material Specification document
<b>O-ring Material</b>	25 mm: EPDM (FDA approved); 12 mm: EPDM (FDA approved)
<b>Surface Quality of Steel</b>	Ra < 0.4 µm (N5)
<b>Serial Number</b>	Yes

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/process-analytics/sensors/237140>

**Spec. Version C**