

Cell Density Integration Kit

Specification Sheet (Part/REF # 243809)



Specifically designed for system integrators, the CDIK includes ComBox, industrial PC, and interfaces for direct connection to the process control system.

Product Specifications

Dimensions (W x D x H)	45 x 163 x 115 mm (without mounting plate)
Analog Output	Optional AUX to Analog Output Box 4-20 mA
Digital Interface	RS485 Modbus (max. 31 addresses)
Operating Voltage	24 VDC
Housing Material	Aluminium, anodized
Measuring Channels	2
Operating Humidity	0 to 80 %
Operating Temperature Range	0 to 55 °C

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/process-analytics/sensors/243809>

Spec. Version B