

# Cell Density Integration Kit

Specification Sheet (Part/REF # 243809)



Specifically designed for system integrators, the CDIK includes ComBox, industrial PC, and interfaces for direct connection to the process control system.

## Product Specifications

<b>Dimensions (W x D x H)</b>	45 x 163 x 115 mm (without mounting plate)
<b>Analog Output</b>	Optional AUX to Analog Output Box 4-20 mA
<b>Digital Interface</b>	RS485 Modbus (max. 31 addresses)
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Aluminium, anodized
<b>Measuring Channels</b>	2
<b>Operating Humidity</b>	0 to 80 %
<b>Operating Temperature Range</b>	0 to 55 °C

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/process-analytics/sensors/243809>

**Spec. Version B**