


# pH Port

Specification Sheet (Part/REF # 243462)



High density polyethylene pH port for single use application together with the OneFerm pH 70 mm sensor.

## Product Specifications

Sensor Family	OneFerm
Parameter	pH
Process Connection	PG13,5
Wetted Parts	HDPE (High Density Polyethylene)
Biocompatibility	Yes, see material specification (upon request)
Shelf Life	12 months prior gamma irradiation. 18 months after gamma irradiation
Autoclavable	No
CIP	No
Steam Sterilizable	No
Gamma Irradiatable	Yes, up to 50 kGy
Operating Temperature Range	4 to 50 °C
Pressure Range bar g	0 to 2 bar
Torque	1.5 Nm (of the OneFerm pH sensor)

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/process-analytics/sensors/243462>

Spec. Version B