

Dummy Sensor 96mm

Specification Sheet (Part/REF # 242540)



Accessories that can be used with all Hamilton housings.

Product Specifications

a-length	96 mm
Process Connection	PG13,5
Wetted Parts	Stainless Steel 1.4435 EPDM (Ethylene propylene elastomer)
O-ring Material	FDA 21 CFR 177.2600; EG 1935/2004; USP <87>; USP <88> Class VI (121 °C)

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/242540>

Spec. Version B