


2.5 m Power Cable VP8 / Lemo

Specification Sheet (Part/REF # 355245-xx)



This guide provides a filterable table for looking up sensor cables for many brands of bioreactors

Product Specifications

Parameter	DO (Optical - ECS)
Electrical Connector	VP8 / Lemo / Power Plug
Length	2.5 m
Max. Diameter	7,5 mm
Material Outer Cover	PVC
Shield	Yes
Operating Temperature Range	-30 to 80 °C
Protection Rating	IP 68 (VP connector)

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/355245-xx>

Spec. Version B