

Arc Modbus Profinet Converter

Specification Sheet (Part/REF # 10116586)



DIN rail mounted converter that allows the Arc Modbus signal to be converted to Profinet in the users Process Control System (PCS)

Product Specifications

Dimensions (W x D x H)	23 x 117 x 100mm
Sensor Compatibility	pH / ORP. DO, Cond, CO2, VCD, TCD
Digital Interface	Profinet
Operating Voltage	10 to 33 VDC
Housing Material	Polyamid
Measuring Channels	4
Operating Temperature Range	-40 to 85 °C
Protection Rating	IP 20

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/10116586>

Spec. Version B