

Septa, 3-Layer, 12.7 mm DIA (12/PK)

Specification Sheet (Part/REF # 76006)



Three Layer Septa is made of preconditioned silicone rubber and is 3.81 mm (0.150 in) thick. The average life of these septa is up to 100 injections with a 26s gauge needle. The maximum operating temperature is 200° C.

Product Specifications

Diameter	12.7 mm (0.500 inch)
Maximum Temperature	200°C / 392°F
Material	Laminated Silicone Rubber
Thickness	3.81 mm (0.150 inch)
Sales Quantity	12 septa per pack

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/gc-septa/76006>

Spec. Version B