

PRP-X600 7 µm 4.6 x 50 mm PEEK

Specification Sheet (Part/REF # 79360)

PRP-X600



PRP-X600 columns give fast separations with better sample capacity of biomolecules.

Product Specifications

Separation Mode	Anion Exchange
Stationary Phase	PRP-X600
Format	HPLC Column
Hardware Inner Diameter	4.6 mm
Hardware Length	50 mm
Particle Size	7 µm
Packing Material Type	PSDVB/Poly (dimethyl amido-propyl methacrylamide)
Pore Size	Superficially Porous
Particle Surface Area (m ² /cm ³)	1.4
Pore Volume (cm ³ /g)	0.0046
Hardware Material	PEEK
Max Pressure	5,000 psi
Exchange Capacity	1.6 meq/gm
Mobile Phase Limits	pH 1-13. 0-100% aqueous, organic modifier
Buffer Strength	0.0-1.0N
Temp Limits	5-30°C
Compound Classification	Labeled/Unlabeled DNA
UOM	1 EACH

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/hplc-columns/79360>

Spec. Version B