

HxSil C18 Semiprep/Preparative Guard Column Starter Kit (1 holder, 1 cartridge), Stainless Steel

Specification Sheet (Part/REF # 79137)



Protect your HxSil C18 column.

Product Specifications

Separation Mode	Reversed-Phase
Stationary Phase	HxSil C18
Format	Guard Cartridge Kit
Hardware Inner Diameter	4.6 mm
Hardware Length	20 mm
Particle Size	10 µm
Packing Material Type	Silica
Guard Column Size	Semiprep/Preparative
Hardware Material	Stainless Steel
Max Pressure	5,000 psi
Mobile Phase Limits	pH 2.0 - 7.5
Compound Classification	General Purpose
UOM	1 holder, 1 cartridge

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/hplc-columns/79137>

Spec. Version B