

# ODO Cap H4

Specification Sheet (Part/REF # 10078261)



Strengthened luminophore matrix for better temperature stability with chemically resistant and hygienic design. Only compatible with the VisiFerm mA.

## Product Specifications

Wetted Parts	Stainless Steel 1.4435 PTFE (Polytetrafluoroethylene) EPDM (Ethylene propylene elastomer) See compliance details in Material Specification document
Surface Quality of Steel	Ra < 0.4 µm (N5)
Serial Number	Yes
Response Time	t98% < 60 s at 25 °C
Autoclavable	Yes, max. Temperature 140 °C
Steam Sterilizable	Yes, max. Temperature 140 °C
Operating Temperature Range	-20 to 140 °C

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/sensors/10078261>

Spec. Version D