

# 3 m Cable K8 / Open End

Specification Sheet (Part/REF # 355154)



K8 Cables with open leads or specialized connectors to mate the pH sensor to bioreactor controllers.

## Product Specifications

|                             |               |
|-----------------------------|---------------|
| Electrical Connector        | K8 / Open End |
| Diameter                    | 5 mm          |
| Length                      | 3 m           |
| Material Outer Cover        | PVC           |
| Operating Temperature Range | -20 to 70 °C  |

Specifications are subject to change without notice  
<https://www.hamiltoncompany.com/sensors/355154>

Spec. Version B