

3 m Cable M12-4 Pole / Open End

Specification Sheet (Part/REF # 355283)



M12 cables for direct connection to 2-wire, 24VDC products such as the VisiFerm mA, VisiTrace mA, and VisiPro Dissolved Oxygen sensors. Open leads for connection to the process control system.

Product Specifications

Electrical Connector	M12-4 Pole A-Coded / Open End
Length	3 m
Max. Diameter	5 mm
Material Outer Cover	PU
Shield	Yes
Operating Temperature Range	-20 to 85 °C
Protection Rating	IP 68 (M12 connector)

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/355283>

Spec. Version B