

5 m Cable M12 - 4 Pole / Open End

Specification Sheet (Part/REF # 355284)



M12 cables for direct connection to 2-wire, 24VDC products such as the VisiFerm mA, VisiTrace mA, and VisiPro Dissolved Oxygen sensors. Open leads for connection to the process control system.

Product Specifications

| | |
|-----------------------------|-------------------------------|
| Electrical Connector | M12-4 Pole A-Coded / Open End |
| Length | 5 m |
| Max. Diameter | 5 mm |
| Material Outer Cover | PU |
| Shield | Yes |
| Operating Temperature Range | -20 to 85 °C |
| Protection Rating | IP 68 (M12 connector) |

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/355284>

Spec. Version B