

FlexiFlow SL 10

Specification Sheet (Part/REF # 237340)



A simple flow-through cell with tubing inlet/outlet connections that can accommodate a single pH or DO sensor.

Product Specifications

For Sensors with	120 mm, 12 mm, PG13,5
Diameter	65 mm
Process Connection	Swagelok 10 mm
Wetted Parts	Stainless Steel 1.4435 EPDM (Ethylene propylene elastomer) See compliance details in Material Specification document
Max. Diameter	65 mm
Max. Total Length	175 mm
Min. Total Length	175 mm
Internal Volume	Approx. 5.5 mL
Mounting	Bottom Screw Mount (4 pcs)
Weight	1200 g
Serial Number	No
Certificate	Yes, 3.1 certificate with heat number
ATEX Approval	II 1/2 G Ex ia IIC T4/T5/T6 Ga/Gb; II 1/2 D ia IIIC T x °C Da/Db
IECEEx Approval	II 1/2 G Ex ia IIC T4/T5/T6 Ga/Gb; II 1/2 D ia IIIC T x °C Da/Db
Autoclavable	No
CIP	No
Steam Sterilizable	Yes
Operating Temperature Range	-10 to 125 °C
Max. Pressure bar g	16 bar

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/237340>

Spec. Version C