

EasyFerm Plus ORP Arc 425

Specification Sheet (Part/REF # 243053)



Arc technology with a variety of sensor length options make this versatile sensor ideal for process control and monitoring in bioprocesses.

Product Specifications

Sensor Family	EasyFerm Plus
Parameter	ORP
Sensor Output	Arc: Modbus, 4 to 20 mA
a-length	425 mm
Electrical Connector	VP8
Measurement Principle	Combination electrode; ORP potential measured against reference
Measuring Range	-1500 mV to +1500 mV
ORP Element	Pt ring
Membrane Shape	Spherical
Diaphragm	HP-Coatramic
Number of Diaphragms	1
Electrolyte	Pressurized Phermlyte
Reference System	Hamilton Everef-F, Silver ion barrier included
Liquid Earth	Yes
Temperature Sensor	NTC 22 kOhm
Configurable Values	ORP: mV; Temperature: °C, K, °F
Diameter	12 mm
Process Connection	PG13,5
Wetted Parts	Platinum Glass Ceramic EPDM (Ethylene propylene elastomer)
Analog Interface 1	4 to 20 mA, programmable
Analog Interface 2	4 to 20 mA for Temp., programmable
Analog Interface 1 and 2	Galvanically not isolated; pulse width modulation 3.5 kHz
Digital Interface	RS485 Modbus (max. 31 addresses)
Baud Rate	4800, 9600, 19200, 38400, 57600, 115200 Bd
Operating Voltage	7 to 30 VDC max. 150 mW
Serial Number	Yes
Recommended Storage	Hamilton Storage Solution or 3 M KCl
Certificate	Yes, with measured value in ORP buffer +475 mV

ATEX Approval	No
IECEX Approval	No
Autoclavable	Yes, max. Temperature 130 °C
CIP	Yes
Steam Sterilizable	Yes, max. Temperature 140 °C
Operating Temperature Range	Analog interface: 0 to 110 °C; Digital interface: 0 to 140 °C
Sample min Conductivity	100 µS/cm

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/sensors/243053>

Spec. Version B