

Cell Density ComBox

Specification Sheet (Part/REF # 243810)



The Cell Density ComBox is a 2-channel USB device that enables the connection of two cell density sensors to the USB port of a Windows PC. The user provided PC must be compatible with the Hamilton cell density software.

Product Specifications

Dimensions (W x D x H)	190 x 85 x 56 mm
Analog Output	Optional AUX to Analog Output Box 4-20 mA
Digital Interface	RS485 Modbus (max. 31 addresses)
Operating System	Works with Windows 7, 8, 10
Operating Voltage	24 VDC
Housing Material	Aluminium, anodized
Measuring Channels	2
Power Supply	24 VDC; 2.5 A
Operating Humidity	0 to 80 %
Operating Temperature Range	-10 to 45 °C

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/243810>

Spec. Version B