

VisiPro DO Ex 425 H2 (discontinued)

Specification Sheet (Part/REF # 243667-152)



VisiPro is ideal for production with a simple 2-wire 4 - 20mA (HART) installation.

Product Specifications

Sensor Family	VisiPro
Parameter	DO (Optical)
Sensor Output	4 to 20 mA / HART
a-length	425 mm
Electrical Connector	M12
Measurement Principle	Oxygen dependent luminescence quenching, temperature compensation
Measuring Range	4 ppb to 25 ppm (DO) 0 to 62.85 %-vol or 0 to 300 %-sat
Accuracy at 25 °C	1 ± 0.05 %-vol: 21 ± 0.2 %-vol; 50 ± 0.5 %-vol
Drift at Room Temperature	< 1 % per week
Sensor Cap	ODO Cap H2
Electrolyte	None
Oxygen Consumption	None
Temperature Sensor	NTC 22 kOhm
Configurable Values	DO: mbar; %-sat; %-vol; µg/l; mg/l; ppb/ppm (gas); ppb/ppm (dissolved oxygen); Temperature: °C
Diameter	12 mm
Process Connection	PG13,5
Wetted Parts	Stainless Steel 1.4435 PTFE (Polytetrafluoroethylene) EPDM (Ethylene propylene elastomer) See compliance details in Material Specification document
Surface Quality of Steel	Ra < 0.4 µm (N5)
4 to 20 mA Current Range	3.5 to 22 mA
Analog Interface 1	Two wire sink 4 to 20 mA for DO, programmable
4 to 20 mA Accuracy	< 0.3 % current value + 0.05 mA
Transmitting Power	Max. 4 dBm
Digital Interface	Bluetooth 4.0 HART Version 7.0
Operating Voltage	18 to 30 VDC
Serial Number	Yes
Response Time	t98% < 60 s at 25 °C
Certificate	Yes, with measured current in air
ATEX Approval	II 1G Ex ia IIC T6/T5/T4/T3 Ga; II 1D Ex ia IIIC T135°C Da

IECEx Approval	II 1G Ex ia IIC T6/T5/T4/T3 Ga; II 1D Ex ia IIIC T135°C Da
Autoclavable	No
CIP	Yes
Steam Sterilizable	Yes, max. Temperature 140 °C
Operating Temperature Range	-20 to 140 °C; the sensor provides no DO reading above 85 °C
Pressure Range bar g	-1 to 12 bar
Protection Rating	IP 68
Required Flow	None

Specifications are subject to change without notice

Spec. Version D

<https://www.hamiltoncompany.com/sensors/243667-152>