

Beverly (discontinued)

Specification Sheet (Part/REF # 817100)



Product Specifications

Measurement Principle	Oxygen dependent luminescence quenching, temperature compensation
Measuring Range	20 ppb to 25 ppm (DO)
Dimensions (W x D x H)	222 x 142 x 322 mm
Operating Temperature Range	0 to 80 °C
Pressure Range bar g	0 to 10 bar
Protection Rating	IP 67

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/817100>

Spec. Version B