

Arc Module SU pH

Specification Sheet (Part/REF # 243233)



Hamilton OneFerm single use pH sensors rely on a proven glass electrode design that has been fully tested for gamma sterilization and dry storage.

Product Specifications

Sensor Family	OneFerm
Electrical Connector	VP8 / VP8
Configurable Values	pH: pH, mV; Temperature: °C, K, °F
Analog Interface 1	4 to 20 mA, programmable
Analog Interface 2	4 to 20 mA, programmable
Digital Interface	RS485 Modbus (max. 31 addresses)
Baud Rate	4800, 9600, 19200, 38400, 57600,115200 Bd
Operating Voltage	7 to 30 VDC max. 150 mW
Serial Number	Yes
ATEX Approval	No
Autoclavable	No
CIP	No
Steam Sterilizable	No
Gamma Irradiatable	No
Operating Temperature Range	0 to 60 °C
Protection Rating	IP 67

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/243233>

Spec. Version B