

EasyFerm Plus PHI VP 325 Pt100

Specification Sheet (Part/REF # 238633-1151)



Traditional sensors offer a standard mV output signal and a wide variety of electrical connectors to work with most transmitters and controllers.

Product Specifications

Sensor Family	EasyFerm Plus
Parameter	pH
Sensor Output	Traditional: mV
a-length	325 mm
Electrical Connector	VP6
Measurement Principle	Combination electrode; pH potential measured against reference
Measuring Range	pH 0 to 14
Sensitivity	57 to 59 mV / pH at 25 °C
Zero Point	0 ± 20 mV
pH Glass	Hamilton Type PHI Glass
pH Glass Resistance	Moderate
Membrane Shape	Spherical
Diaphragm	HP-Coatramic
Number of Diaphragms	1
Electrolyte	Pressurized Phermlyte
Reference System	Hamilton Everef-F, Silver ion barrier included
Liquid Earth	No
Temperature Sensor	Pt100
Diameter	12 mm
Process Connection	PG13,5
Wetted Parts	Glass EPDM (Ethylene propylene elastomer)
Serial Number	Yes
Recommended Storage	Hamilton Storage Solution or 3 M KCl
Certificate	Yes, with measured values in Buffer pH 4.01 and pH 7.00
ATEX Approval	II 1/2 G Ex ia IIC T4/T5/T6 Ga/Gb; II 1/2 D ia IIIC T x °C Da/Db
IECEx Approval	II 1/2 G Ex ia IIC T4/T5/T6 Ga/Gb; II 1/2 D ia IIIC T x °C Da/Db
Autoclavable	Yes
CIP	Yes
Steam Sterilizable	Yes
Operating Temperature Range	0 to 140 °C

Sample min Conductivity	100 µS/cm
Pressure Range bar g	0 to 6 bar