


# pH Port

Specification Sheet (Part/REF # 243462)



OneFerm pH sensors are offer multiple electrical connector options and sensor lengths to work with most single use bags and bioreactor installations.

## Product Specifications

<b>Sensor Family</b>	OneFerm
<b>Parameter</b>	pH
<b>Process Connection</b>	PG13,5
<b>Wetted Parts</b>	HDPE (High Density Polyethylene)
<b>Biocompatibility</b>	Yes, see material specification (upon request)
<b>Shelf Life</b>	12 months prior gamma irradiation. 18 months after gamma irradiation
<b>Autoclavable</b>	No
<b>CIP</b>	No
<b>Steam Sterilizable</b>	No
<b>Gamma Irradiatable</b>	Yes, up to 50 kGy
<b>Operating Temperature Range</b>	4 to 50 °C
<b>Pressure Range bar g</b>	0 to 2 bar
<b>Torque</b>	1.5 Nm (of the OneFerm pH sensor)

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/sensors/243462>

**Spec. Version B**