

3-3 PTFE, HV, TLL, PSD Valve

Specification Sheet (Part/REF # 58889-01)



Product Specifications

Valve Model	3-3
Valve Model Description	"T" Flow Path 3-ports
Fluid Path	PTFE/CTFE
Valve Size	HV
Nominal Port Diameter	0.060 inch (1.5 mm)
Valve Outer Body Dimension	19.1 mm (0.75 inch)
Housing Material	Aluminum
Actuated	PSD/4, PSD/6
Break Away Torque	15 oz-in (105.9 mNm)
Panel Mounting	No
Thread Depth	5.7 mm (0.226 inch)
Threaded Connection	¼-28
Operating Temp. High	38 °C (100 °F)
Operating Temp. Low	-12 °C (10 °F)
Operating Pressure	0 to 100 psig (0 to 6.9 bar)
Storage Temp. High	38 °C (100 °F)
Storage Temp. Low	-18 °C (0 °F)
Compatible Syringe	Luer Lock (TLL)

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/valves/58889-01>

Spec. Version B