

# 3-3 Hamaflon™, HV, Luer Lock (TLL), PSD Valve

Specification Sheet (Part/REF # 99892-01)



## Product Specifications

Valve Model	3-3
Valve Model Description	"T" Flow Path 3-ports
Fluid Path	CTFE/Hamaflon
Valve Size	HV
Nominal Port Diameter	0.059 inch (1.5 mm)
Housing Material	CTFE
Actuated	PSD/4, PSD/6
Break Away Torque	25 oz-in (176 mNm)
Panel Mounting	No
Panel Thickness	N/A
Thread Depth	0.250 (6.35 mm)
Threaded Connection	¼-28
Operating Temp High	40 °C (104 °F)
Operating Temp Low	15 °C (59 °F)
Operating Pressure	0 to 100 psig (0 to 6.9 bar)
Storage Temp High	65 °C (149 °F)
Storage Temp Low	-29 °C (-20 °F)
Compatible Syringe	PTFE Luer Lock (TLL)

Specifications are subject to change without notice

<https://www.hamiltoncompany.com/valves/99892-01>

Spec. Version B