

Arc Modbus OPC Converter

Specification Sheet (Part/REF # 10089359)



The Modbus OPC module converts the Modbus protocol into OPC. All Arc parameters are supported. The conversion script is pre-installed.

Product Specifications

Dimensions (W x D x H)	11 x 8.3 x 6.6 cm
Sensor Compatibility	pH / ORP, DO, CO2, VCD, TCD
Digital Interface	Ethernet connection with RJ45 (OPC UA) MicroSD card
Operating Voltage	12 VDC
Housing Material	Aluminium, powder-coated
Power Supply	12VDC, 3A
Operating Humidity	5 to 95 %
Operating Temperature Range	0 to 45 °C
Sensor Connectors	4
Ingress Protection	IP30

Specifications are subject to change without notice
<https://www.hamiltoncompany.com/sensors/10089359>

Spec. Version C